

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Monoclonal Anti-Fibronectin antibody produced in mouse - clone FN-15, ascites fluid

Product Number: F7387

Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Very Faint Yellow to Very Dark Yellow to Very Dark Brown
Protein by Biuret	15 - 55 mg/ml
Mouse IgG1 by RID	5.0 - 10.0 mg/ml
ELISA - Titer	1:5,000-1:10,000
WB-Western Blot-Protein	Fibronectin from human plasma
WB Titer	1:800-1:1600
ICC/IF Cells	HS-68 Human Foreskin Fibroblasts Cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Titer	1:200-1:400
Recommended Retest Period	-----
5 Years	

Specification: PRE.0.ZQ5.10000020778

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.