


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Diphenylamine – ReagentPlus®, 99%

Product Number: **112763**
CAS Number: 122-39-4
MDL: MFCD00003014
Formula: C₁₂H₁₁N
Formula Weight: 169.22 g/mol



TEST

Specification

Appearance (Color)

Appearance (Form)

Infrared spectrum

Purity (GC)

White to Yellow to Beige

Powder or Flake or Crystals or

Crystalline Chunk(s)

Conforms to Structure

≥ 98.5 %

Specification: PRD.2.ZQ5.10000043339

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.