


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Sesamol - $\geq 97\%$, from *Sesamum indicum* (sesame)

Product Number: SMB00701
CAS Number: 526-07-8



Formula: C₂₀H₁₈O₇
Formula Weight: 370.36 g/mol
Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Powder
Appearance (Colour)	White to Off White
Solubility (Solvent)	Dimethylsulfoxide
Solubility (Conc)	0.95 - 1.05 mg/ml
Solubility (Turbidity)	Clear
Solubility (Color)	Colorless
Purity (HPLC)	$\geq 97.0 \%$
Proton NMR spectrum	Conforms to Structure
NMR (Residual Solvent 1)	Acetone
NMR (% Solvent 1)	$\leq 1.00 \%$
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000015915

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.