

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Phenol:Chloroform:Isoamyl Alcohol 25:24:1 – for molecular biology

Product Number:

**P3803**

Storage Temperature:

2 - 8 °C

TEST	Specification
Appearance	Pass
Colorless 2 layer liquid	
% Purity	≥ 99.0
UV Absorbance 330nm	≤ 0.2
UV Absorbance 405nm	≤ 0.1
UV Absorbance 510nm	≤ 0.1
pH	6.5 - 6.9
at 25 deg. C	
DNase, RNase, and Protease	None Detected

Specification: PRD.0.ZQ5.10000022023

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.