

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Anti-Sheep IgG (whole molecule)-Alkaline Phosphatase antibody produced in donkey - affinity isolated antibody, buffered aqueous glycerol solution

Product Number: **A5187**

MDL: MFCD00162844

Storage Temperature: 2 - 8 °C

TEST	Specification
------	---------------

Appearance (Turbidity)	Clear
Appearance (Color)	Colorless to Yellow
Appearance (Form)	Solution
Protein Content	0.5 - 8.0 mg/ml
Conjugate concentration prior to the addition of BSA	
Direct ELISA Titer-Sheep IgG	30000 - 60000
Working Dilution 1:30,000 - 1:60,000 versus 5 µg/ml sheep IgG	
Dot Blot Detects Sheep IgG	≤ 20 ng
Dot Blot detects minimum of 20 ng sheep IgG at a 1:30,000 dilution	

Specification: PRD.1.ZQ5.10000017525

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.