

3050 Spruce Street, Saint Louis, MO 63103, USA  
Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)  
Email USA: [techserv@sial.com](mailto:techserv@sial.com)  
Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

Product Specification

Product Name:  
Anti-Mouse IgG (whole molecule)–FITC antibody produced in rabbit – IgG fraction of antiserum, buffered aqueous solution  
Product Number: F9137

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Yellow
IgG Concentration (OD 280nm)	10.0 - 20.0 mg/ml
F/P Molar Ratio	2.5 - 6.5
IF Cells	Human periferal blood lymphocytes
IF-Titer	1:100-1:200
IHC - Tissue	Human Appendix or Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:100-1:200
Recommended Retest Period	-----
3 Years	

Specification: PRE.0.ZQ5.10000015071

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.