

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Anti-Actin antibody produced in rabbit – affinity isolated antibody, buffered aqueous solution

Product Number: A2066

Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	0.4 - 0.8 mg/ml
WB-Cell Line/Tissue Extract	Chicken Gizzard Extract
WB Titer	1:100-1:200
ICC/IF Cells	Chicken Fibroblast
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Titer	1:40-1:80
IHC - Tissue	Human Appendix or Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:25-1:50
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000015086

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.