

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name: Monoclonal Anti-Human IgM (μ-chain specific)–Alkaline Phosphatase antibody produced in mouse – clone MB-11, purified immunoglobulin, buffered aqueous glycerol solution
Product Number: A2189

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Almost Colorless to Light Yellow
IgG Concentration (OD 280nm)	1.5 - 2.5 mg/ml
ELISA - Titer	1:35,00-1:45,000
Dot Blot-Titer	1:20,000-1:40,000
NBT/BCIP	
Dot Blot-Titer	1:30,000-1:60,000
chemiluminescence	
Recommended Retest Period	-----
2 Years	

Specification: PRE.1.ZQ5.10000015973

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.