

3050 Spruce Street, Saint Louis, MO 63103, USA  
Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)  
Email USA: [techserv@sial.com](mailto:techserv@sial.com)  
Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

Product Specification

Product Name:  
Anti-Mouse IgG (Fab specific) F(ab')<sub>2</sub> fragment antibody produced in goat – affinity isolated antibody

Product Number: M0659

Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
F(ab) <sub>2</sub> Concentration(OD 280nm)	2.0 - 2.5 mg/ml
ELISA CrossRxn Mouse IgG	100 - 100 %
ELISA CrossRxn Mouse Fab	≥ 30.0 %
ELISA CrossRxn Mouse Fc	≤ 10.0 %
ELISA CrossRxn Human IgG	≤ 10.0 %
ELISA CrossRxn Human IgM	≤ 10.0 %
ELISA CrossRxn Human IgA	≤ 10.0 %
ELISA CrossRxn Bovine IgG	≤ 10.0 %
ELISA CrossRxn Bovine IgM	≤ 10.0 %
ELISA CrossRxn Horse IgG	≤ 10.0 %
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000017017

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.