

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Urease from Canavalia ensiformis (Jack bean)

Product Number: **U7752**  
CAS Number: 9002-13-5  
MDL: MFCD00070858

Storage Temperature: -20 °C

TEST	Specification
Appearance (Color)	White
Appearance (Form)	Solid
Solubility (Turbidity)	Clear to Slightly Hazy
Solubility (Form)	Liquid
Solubility (Color)	Colorless to Faint Yellow
mg protein/vial (Biuret)	0.9 - 1.4
Suitability	Suitable
Suitable for use as a molecular weight marker in a non-denaturing PAGE system, approximate molecular mass 272 kDa (trimer) and 545 kDa (hexamer).	

Specification: PRD.3.ZQ5.10000018542

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.