

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Oncostatin M from mouse - BioReagent, ≥97% (SDS-PAGE), recombinant, expressed in E. coli, lyophilized powder, suitable for cell culture

Product Number:

O1637

CAS Number:

106956-32-5

MDL:

MFCD01094784

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Formulation	Conforms
Lyophilized from 0.2 um-filtered Phosphate buffered saline containing 50 ug BSA per ug OSM	
Bioactivity	Conforms
(Cell proliferation, NIH/3T3 CELLS)	
EC50: 0.25 - 1 ng/ml	
Purity by SDS Electrophoresis	≥ 97 %
Endotoxin Assay	Conforms
< or = 1.0 EU/UG OSM	

Specification: PRD.0.ZQ5.10000046653

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.