

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
α-Melanocyte stimulating hormone - ≥97% (HPLC)

Product Number: M4135
CAS Number: 581-05-5

Formula: C77H109N21O19S
Formula Weight: 1.664,88 g/mol
Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Powder
Appearance (Color)	White
Solubility (Solvent)	Water
Solubility (Conc)	1.00 - 1.04 mg/ml
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
Molecular Weight (MS)	1662.9 - 1666.9
Peptide Content (AAA)	≥ 70.0 %
Purity (HPLC)	≥ 97.0 %
Recommended Retest Period	-----
3 Years	

Specification: PRE.1.ZQ5.10000014697

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.