

3050 Spruce Street, Saint Louis, MO 63103, USA  
Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)  
Email USA: [techserv@sial.com](mailto:techserv@sial.com)  
Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

Product Specification

Product Name:  
Anti-Histone H3 antibody produced in rabbit – IgG fraction of antiserum, buffered aqueous solution

Product Number: H0164

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	8.0 - 12.0 mg/ml
WB-Cell Line/Tissue Extract	A431 Human epithelial carcinoma cells
WB-Western Blot Titer	1:5,000-1:10,000
WB-Cell Line/Tissue Extract	NIH-3T3 Mouse Fibroblasts
WB-Western Blot Titer	1:5,000-1:10,000
WB-Cell Line/Tissue Extract	PC-12 cells
WB-Western Blot Titer	1:2500-1:5000
ICC/IF Cells	NIH-3T3 Mouse Fibroblasts
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Titer	1:250-1:500
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000020683

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.