

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Dulbecco's Modified Eagle's Medium/Nutrient Mixture F-12 Ham - With L-glutamine and 15 mM HEPES, without sodium bicarbonate and phenol red, powder, suitable for cell culture

Product Number:**D2906****MDL:**

MFCD00217417

Storage Temperature:

2 - 8 °C

TEST**Specification**

Origin	Non-Animal Source
Osmolality with 1.2 g/L NaHCO ₃	285 - 315 mOs/kg
Osmolality	263 - 290 mOs/kg
Water (by Karl Fischer)	≤ 2.0 %
pH with 1.2 g/L NaHCO ₃	6.6 - 7.2
pH	5.5 - 6.1
Solubility (Turbidity)	Clear
Solubility (Form) at 15.6 g/L H ₂ O	Solution
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Cell Culture Test	Pass
Total Glucose	18.3 - 22.3 %
Endotoxin Level at 1x	≤ 1.0 EU/ml

Specification: PRD.1.ZQ5.10000013195

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.