

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti- β -Actin antibody, Mouse monoclonal - clone AC-15, purified from hybridoma cell culture

Product Number:

A1978

Storage Temperature:

-20 °C

TEST**Specification**

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	2.0 - 2.5 mg/ml
WB-Cell Line/Tissue Extract	HS-68 Human Fibroblast or Chicken Fibroblast
WB Working Concentration	0.5 - 1.0 μ g/ml
ICC/IF Cells	HS-68 Human Fibroblast or Chicken Fibroblast
ICC/IF Fixation Reagent 1	Methanol
ICC/IF-Fixation Reagent 2	Acetone
ICC/IF-Working Concentration	10 - 40 μ g/ml
Recommended Retest Period	-----
5 Years	

Specification: PRE.0.ZQ5.10000014082

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.