

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Arachidonic acid – from non-animal source, ≥98.5% (GC)

Product Number:

A3611

CAS Number:

506-32-1

Formula:


C₂₀H₃₂O₂

Formula Weight:

304.47 g/mol

Storage Temperature:

-20 °C



TEST

Specification

Appearance (Turbidity)

Clear

Appearance (Color)

Colorless to Very Faint Yellow

Appearance (Form)

Liquid

Infrared spectrum

Conforms to Structure

Purity (GC)

≥ 98.5 %

Recommended Retest Period

6 Years

Specification: PRD.1.ZQ5.10000017417

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.