

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Hanks' Balanced Salt solution – Modified, with sodium bicarbonate, without phenol red, liquid, sterile-filtered, suitable for cell culture

Product Number:

H8264

TEST	Specification
Appearance (Turbidity)	Clear
Appearance (Form)	Solution
pH	7.1 - 7.5
Osmolality	266 - 294 mOs/kg
Salt Toxicity Test	Pass
Cell Line	Cell Line - Cell Types
Sterility by USP guidelines & by EP Guildelines	Negative
Endotoxin Level	≤ 1 EU/ml
Glucose Concentration	0.9 - 1.1 g/l
Site of Manufacturing	Broadway

Remarks:

Date of Manufacture: (DDMMYY)

Specification: PRD.0.ZQ5.10000102897

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

