


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
o-Dianisidine

**Product Number:** D9143  
**CAS Number:** 119-90-4  
**MDL:** MFCD00008372  
**Formula:** C<sub>14</sub>H<sub>16</sub>N<sub>2</sub>O<sub>2</sub>  
**Formula Weight:** 244.29 g/mol



### TEST

### Specification

Appearance (Color)

Light Yellow to Very Dark Yellow and

Appearance (Form)

Light Brown to Brown and Pink

Infrared spectrum

Powder

Solubility (Color)

Conforms to Structure

10 mg Plus 1 ml of Ethanol

Light Yellow to Very Dark Yellow and

Solubility (Turbidity)

Light Brown to Brown and Pink

Carbon

Clear

Nitrogen

67.5 - 70.2 %

11.2 - 11.7 %

Specification Date : 04/26/2011

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.