

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Alkaline Hypochlorite solution

Product Number: A1727

Storage Temperature: 2 - 8 °C

TEST	Specification
Suitability	Suitable
Suitable for quantitation of urea nitrogen.	
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless to Slightly Yellow
Appearance (Form)	Liquid
Normality by Titration (HCl)	0.600 - 0.650

Specification: PRD.1.ZQ5.10000011784

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.