

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Mouse IgG (whole molecule)-FITC antibody produced in sheep – affinity isolated antibody, buffered aqueous solution

Product Number: **F3008**

MDL: MFCD00162642

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Turbidity)	Clear
Appearance (Color)	Faint Yellow to Yellow
Appearance (Form)	Liquid
F/P Molar Ratio	3.0 - 5.0
Conjugate concentration prior to the addition of BSA	
A280/A496 UV Absorption	1.0 - 1.5
Conjugate concentration prior to the addition of BSA	
Protein Content	1.1 - 1.1 mg/ml
Conjugate concentration prior to the addition of BSA	
Immunofluorescence (Direct)	Minimum Dilution 1:32
Using Mouse Spleen Cells	

Specification: PRD.2.ZQ5.10000023338

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.