


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
1-Azidoadamantane - 97%

Product Number: 276219  
CAS Number: 24886-73-5  
MDL: MFCD00074793  
Formula: C<sub>10</sub>H<sub>15</sub>N<sub>3</sub>  
Formula Weight: 177.25 g/mol  
Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Crystal to Powder
Infrared spectrum	Conforms to Structure
Carbon	65.4 - 70.1 %
Nitrogen	22.8 - 24.5 %
Purity (GC)	≥ 96.5 %

**Remarks:**

Reviewing Chemist :

Specification: PRD.0.ZQ5.10000021160

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.