

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Catalase from bovine liver – aqueous solution,  $\geq 30,000$  units/mg protein

Product Number:

**C3155**

CAS Number:

9001-05-2

MDL:

MFCD00081483

Storage Temperature:

2 - 8 °C

TEST	Specification
------	---------------

mg protein/ml (UV)

 $\geq 10.0$ 

E1% at 405 nm

units/mg protein

 $\geq 30000$ 

Unit definition: One unit will decompose 1.0 micromole of hydrogen peroxide per minute at pH 7.0 at 25 deg C, while the hydrogen peroxide concentration falls from 10.3 to 9.2 millimolar.

Thymol Content

 $\leq 0.10$  mg/ml

Aseptically Filled

Pass

Specification: PRD.1.ZQ5.10000036228

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.