

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:

Niclosamide

Product Number:

N3510

CAS Number:


50-65-7

Formula:

C<sub>13</sub>H<sub>8</sub>Cl<sub>2</sub>N<sub>2</sub>O<sub>4</sub>

Formula Weight:

327,12 g/mol



TEST	Specification
Appearance (Color)	Conforms
Off White to Yellow	
Appearance (Form)	Powder
Assay	98.0 - 101.0 %
End-point potentiometrically titration (dried substance)	
Identification	Conforms
Test B BP (Infrared absorption spectrophotometry)	
Identification	Conforms
Test E BP (Loss on drying)	
Related Substances	≤ 0.2 %
Melting Point	227 - 232 °C
Loss on Drying	≤ 0.5 %
Sulphated Ash	≤ 0.1 %
Recommended Retest Period	-----
4 Years	

Specification: PRE.2.ZQ5.10000010578

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.