

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Escherichia coli – Strain K12, lyophilized cells

Product Number:

EC1

MDL:

MFCD00131026

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

units/G solid

≥ 100

Alkaline phosphatase

One DEA unit will hydrolyze 1 micromole of 4-nitrophenyl phosphate per minute at pH 9.8 at 37 deg C.

Specification: PRD.0.ZQ5.10000035021

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.