

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:


Phenazine methosulfate - ≥90% (UV)

Product Number:

P9625

CAS Number:

299-11-6



Formula:

C₁₄H₁₄N₂O₄S

Formula Weight:

306,34 g/mol

Storage Temperature:

-20 °C

TEST

Specification

Appearance (Color)

Yellow to Dark Yellow and Brown to Dark Brown

Appearance (Form)

Powder

Assay (UV)

≥ 90 %

(lambda max 387.5 nm, H₂O)

Solubility (Color)

Faint Brown to Brown to Orange

(800 mg + 4 ml H₂O)

Solubility (Turbidity)

Clear

Expiration Date Period

2 Years

Specification: PRE.6.ZQ5.10000010566

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.