

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
ExtrAvidin® -Alkaline Phosphatase – buffered aqueous solution

Product Number: E2636

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Almost Colorless to Light Yellow
Conjugate Concentration (P+ E)	≥ 3.0 mg/ml
ELISA - Titer	1:60,000-1:70,000
Dot Blot-Titer	1:300,000-1:500,000
IHC - Tissue	Human Appendix or Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:100-1:200
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000015298

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.