


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Fenchyl acetate, mixture of  $\alpha$ - and  $\beta$ - -  $\geq 96\%$ , FG

Product Number: **W339008**  
CAS Number: 13851-11-1  
MDL: MFCD00083571  
Formula: C<sub>12</sub>H<sub>20</sub>O<sub>2</sub>  
Formula Weight: 196.29 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 °C	1.454 - 1.458
Infrared spectrum	Conforms to Structure
Purity (GC)	$\geq 96.0\%$
Mixture of Isomers	
Specific Gravity at 25 deg C	0.966 - 0.975
Arsenic (As)	$\leq 3$ ppm
Cadmium (Cd)	$\leq 1$ ppm
Mercury (Hg)	$\leq 1$ ppm
Lead (Pb)	$\leq 10$ ppm
Expiration Date Period 5 Years	-----

Specification: PRD.4.ZQ5.10000004147

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.