

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Oleoyl chloride - ≥99% (GC)

Product Number: O0876
CAS Number: 112-77-6
MDL: MFCD00134332
Formula: C18H33OCl
Formula Weight: 300.91 g/mol
Storage Temperature: -20 °C



TEST	Specification
Appearance (Color)	Colorless
Appearance (Turbidity)	Clear
Appearance (Form)	Liquid
Proton NMR spectrum	Conforms to Structure
Purity (GC)	≥ 98.5 %
Recommended Retest Period	-----
3 Years	

Specification: PRD.0.ZQ5.10000043969

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.