

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name: Vitronectin human – recombinant, expressed in HEK 293 cells, ≥95% (SDS–PAGE), ≥95% (HPLC), cell culture tested
Product Number: SRP3186

Storage Temperature: -20 °C

TEST	Specification
Appearance (Form)	Powder
Appearance (Color)	White to Off White
Vial Content(Bradford)	250 - 325 µg
Purity by SDS-PAGE	≥ 95 %
Purity by HPLC	≥ 95.0 %
Attachment	Pass
Endotoxin Level	≤ 1 EU/ug
Recommended Retest Period	-----
2 Years	

Specification: PRE.0.ZQ5.10000017086

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.