

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
des-Arg<sup>9</sup>-[Leu<sup>8</sup>]-Bradykinin acetate salt - ≥97% (HPLC)

Product Number: **B6769**  
CAS Number: 115035-45-5  
MDL: MFCD00133250  
Formula: C<sub>41</sub>H<sub>63</sub>N<sub>11</sub>O<sub>10</sub>  
Formula Weight: 870.01 g/mol  
Storage Temperature: -20 °C



TEST	Specification
------	---------------

Appearance (Color)	White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
5 mg/mL H <sub>2</sub> O	
Water (by Karl Fischer)	≤ 9.0 %
% Acetate	2.9 - 15.0
% Peptide content	≥ 70
Purity (HPLC)	≥ 97 %

Note

Formula and formula weight are for the free base

Specification: PRD.2.ZQ5.10000010029

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.