

3050 Spruce Street, Saint Louis, MO 63103, USA  
Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)  
Email USA: [techserv@sial.com](mailto:techserv@sial.com)  
Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

Product Specification

Product Name:  
MegaCell™ RPMI-1640 Medium - without L-glutamine, liquid, sterile-filtered, suitable for cell culture

Product Number: M3817

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Turbidity)	Clear
Appearance (Form)	Solution
pH	7.0 - 7.6
Osmolality	280 - 320 mOs/kg
Sterility	Negative
by USP	
Amino Acid Analysis	Pass
Glucose	2.46 - 2.72 g/l
Endotoxin Level	≤ 2.0 EU/ml
ICP Major Analysis	Pass
Cell Culture Test	Pass

Specification: PRD.0.ZQ5.10000038972

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.