


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Hydroxyurea - 98%, powder

Product Number: H8627
CAS Number: 127-07-1
MDL: MFCD00007943
Formula: CH₄N₂O₂
Formula Weight: 76.05 g/mol
Storage Temperature: 2 - 8 °C



TEST

Specification

Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Color)	Colorless to Faint Yellow to Pink
Solubility (Turbidity)	Clear
50 mg/mL, H ₂ O	
% Purity	≥ 98
by Elemental Analysis	

Specification: PRD.0.ZQ5.10000036509

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.