

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
DL-3,4-Dihydroxyphenyl glycol

Product Number: **D9753**
CAS Number: 28822-73-3
MDL: MFCD00004702
Formula: C₈H₁₀O₄
Formula Weight: 170.16 g/mol
Storage Temperature: -20 °C

TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 95 %
Solubility (Color)	Colorless to Light Yellow
Solubility (Turbidity)	Clear
50 mg/mL H ₂ O	

Specification: PRD.0.ZQ5.10000052264

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.