

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Anti-Neurofilament 200 antibody produced in rabbit – IgG fraction of antiserum, buffered aqueous solution

Product Number: N4142

Storage Temperature: -20 °C

| TEST | Specification |
|------------------------------|---------------------------------------|
| Appearance (Form) | Liquid |
| Appearance (Turbidity) | Clear |
| Appearance (Color) | Colorless |
| IgG Concentration (OD 280nm) | 8.0 - 16.0 mg/ml |
| WB-Cell Line/Tissue Extract | Rat Brain/Bovine Spinal Cord |
| | Neurofilaments |
| WB Titer | 1:1000-1:2000 |
| IHC - Tissue | Rat Cerebellum |
| IHC - Fixation | FFPE-Formalin Fixed Paraffin Embedded |
| IHC - Titer | 1:80-1:160 |
| Recommended Retest Period | ----- |
| 4 Years | |

Specification: PRE.0.ZQ5.10000016192

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.