


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
2-Aminobenzaldehyde - ≥98%

Product Number: **A9628**  
CAS Number: 529-23-7  
MDL: MFCD00007709  
Formula: C<sub>7</sub>H<sub>7</sub>NO  
Formula Weight: 121.14 g/mol  
Storage Temperature: -20 °C



TEST	Specification
Appearance (Color)	Yellow to Yellow-Green
Appearance (Form)	Powder
Solubility (Color)	Yellow to Yellow-Green
Solubility (Turbidity)	Clear to Very Slightly Hazy
25 mg/mL, EtOH	
Carbon	68.0 - 70.8 %
Nitrogen	11.3 - 11.8 %
Infrared spectrum	Conforms to Structure
Purity (HPLC)	≥ 98 %

Specification: PRD.0.ZQ5.10000041447

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.