

3050 Spruce Street, Saint Louis, MO 63103, USA
Website: www.sigmaaldrich.com
Email USA: techserv@sial.com
Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Anti-Vinculin antibody, Mouse monoclonal – clone hVIN-1, purified from hybridoma cell culture

Product Number: V9264

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	1.0 - 1.5 mg/ml
WB-Cell Line/Tissue Extract	HS-68 Human Foreskin Fibroblasts Cells
WB Working Concentration	0.05 - 0.10 µg/ml
ICC/IF Cells	HS-68 Human Foreskin Fibroblasts Cells
ICC/IF Fixation Reagent 1	3%-4% Paraformaldehyde
ICC/IF-Fixation Reagent 2	0.5% Triton X-100
ICC/IF-Working Concentration	5 - 10 µg/ml
Recommended Retest Period	-----
4 Years	

Specification: PRE.0.ZQ5.10000016463

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.