


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Naphthol AS-D chloroacetate – esterase substrate

Product Number: **N0758**  
CAS Number: 35245-26-2  
MDL: MFCD00042714  
Formula: C<sub>20</sub>H<sub>16</sub>ClNO<sub>3</sub>  
Formula Weight: 353.80 g/mol  
Storage Temperature: -20 °C



TEST	Specification
Appearance (Color)	White to Off White
Appearance (Form)	Powder
Solubility (Color)	Colorless to Faint Yellow
Solubility (Turbidity)	Clear
50 mg/ml, Acetone	
<sup>1</sup> H NMR Spectrum	Conforms to Structure
Carbon	66.5 - 69.3 %
Nitrogen	3.8 - 4.1 %
Purity (TLC)	≥ 98 %

Specification: PRD.2.ZQ5.10000008557

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.