


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Octanoic acid - ≥98%, FG

Product Number: **W279900**  
CAS Number: 124-07-2  
MDL: MFCD00004429  
Formula: C<sub>8</sub>H<sub>16</sub>O<sub>2</sub>  
Formula Weight: 144.21 g/mol



TEST	Specification
Appearance (Color)	Colorless to Light Yellow
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.426 - 1.430
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 98.0 %
Specific Gravity (at 25 deg C)	0.890 - 0.930
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Organoleptics	Pass
Expiration Date Period 5 Years	-----

Specification: PRD.4.ZQ5.10000005645

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

