

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Human IgG (Fab specific), F(ab')₂ fragment antibody produced in goat - affinity isolated antibody, buffered aqueous solution

Product Number:

I3266

TEST	Specification
Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Colorless
IgG Concentration (OD 280nm)	2.0 - 2.5 mg/ml
ELISA CrossRxn Human IgG	100 - 100 %
ELISA CrossRxn Human Fab	≥ 30.0 %
ELISA CrossRxn Human FC	≤ 10.0 %
ELISA CrossRxn Human IgM	≥ 30.0 %
ELISA CrossRxn Human IgA	≥ 30.0 %
ELISA CrossRxn Human K+ L	≥ 30.0 %
ELISA CrossRxn Mouse IgG	≤ 10.0 %
ELISA CrossRxn Rat IgG	≤ 10.0 %
Recommended Retest Period	-----
4 Years	

Specification: PRE.1.ZQ5.10000016052

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.