

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:Fractalkine, Extracellular Domain human - $\geq 97\%$ (SDS-PAGE), recombinant, expressed in mouse NS0 cells, cell culture tested, lyophilized powder**Product Number:**

F135

MDL:

MFCD02098545

Storage Temperature:

-20 °C

TEST	Specification
------	---------------

Formulation	Conforms
Lyophilized from a 0.2 μm -filtered solution in PBS containing 50 μg bovine serum albumin per 1 μg of cytokine.	
Bioactivity	
EC50: Report Result	
Measured by its ability to chemoattract freshly isolated peripheral blood lymphocytes or mouse BaF/3 cells transfected with hCX3CR-1.	
Purity by SDS Electrophoresis	Conforms
> / = 97%	
Endotoxin Level	Conforms
< / = 1 EU/ μg Fractalkine	

Specification: PRD.0.ZQ5.10000015716

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.