

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)


Email USA: [techserv@sial.com](mailto:techserv@sial.com)

Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Octyl formate - ≥97%, FCC

**Product Number:** W280909  
**CAS Number:** 112-32-3  
**MDL:** MFCD00046147  
**Formula:** C<sub>9</sub>H<sub>18</sub>O<sub>2</sub>  
**Formula Weight:** 158.24 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.418 - 1.420
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 97.00 %
Specific Gravity	0.869 - 0.874
Acid Value	≤ 1.0 ml
Solubility (Turbidity) c = 1ml/5ml; 70% Ethanol Remains Clear Diluted to 10ml	Clear
Solubility (Color)	Colorless
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period 5 Years	-----

Specification: PRD.0.ZQ5.10000100961

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.