


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaldrich.com](http://www.sigmaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Acetylcholine iodide - ≥97%

**Product Number:** A7000  
**CAS Number:** 2260-50-6  
**MDL:** MFCD00011815  
**Formula:** C<sub>7</sub>H<sub>16</sub>INO<sub>2</sub>  
**Formula Weight:** 273.11 g/mol  
**Storage Temperature:** -20 °C



### TEST

### Specification

Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Turbidity) c = 100 mg/ml; Water	Clear to Very Slightly Hazy
Solubility (Color)	Colorless to Faint Yellow
Purity (TLC)	≥ 98 %
Titration with AgNO <sub>3</sub>	≥ 97 %
Recommended Retest Period	-----
3 years	

Specification: PRD.2.ZQ5.10000004098

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.