

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Mouse IgG (Fc specific)-FITC antibody produced in goat - affinity isolated antibody, buffered aqueous solution

Product Number:

F5387

TEST	Specification
------	---------------

Appearance (Form)	Liquid
Appearance (Turbidity)	Clear
Appearance (Color)	Yellow
IgG Concentration (OD 280nm)	3.0 - 6.5 mg/ml
F/P Molar Ratio	2.5 - 6.5
IF Cells	Human periferal blood lymphocytes
IF-Titer	1:32-1:64
IHC - Tissue	Human Appendix or Human Tonsil
IHC - Fixation	FFPE-Formalin Fixed Paraffin Embedded
IHC - Titer	1:100-1:200
Recommended Retest Period	-----
3 Years	

Specification: PRE.0.ZQ5.10000017063

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.