


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Phenethyl formate - ≥96%, FG

Product Number: W286400
CAS Number: 104-62-1
MDL: MFCD00021046
Formula: C₉H₁₀O₂
Formula Weight: 150.17 g/mol
Storage Temperature: 2 - 8 °C



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Infrared Spectrum	Conforms to Structure
Refractive index at 20 °C	1.505 - 1.509
Color Test	≤ 100 APHA
Purity (GC)	≥ 96.0 %
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.1.ZQ5.10000070306

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.