


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: [www.sigmaaldrich.com](http://www.sigmaaldrich.com)Email USA: [techserv@sial.com](mailto:techserv@sial.com)Outside USA: [eurtechserv@sial.com](mailto:eurtechserv@sial.com)

## Product Specification

Product Name:  
Geranyl acetate - natural, FCC

**Product Number:** W250910  
**CAS Number:** 105-87-3  
**MDL:** MFCD00015037  
**Formula:** C<sub>12</sub>H<sub>20</sub>O<sub>2</sub>  
**Formula Weight:** 196.29 g/mol



| TEST                       | Specification         |
|----------------------------|-----------------------|
| Appearance (Color)         | Colorless             |
| Appearance (Form)          | Liquid                |
| Refractive index at 20 ° C | 1.458 - 1.464         |
| Infrared spectrum          | Conforms to Structure |
| Specific Gravity           | 0.900 - 0.914         |
| Ester Content              | ≥ 90.00 %             |
| Solubility (Turbidity)     | Clear                 |
| 1ml/9ml 70% Ethanol        |                       |
| Solubility (Color)         | Colorless             |
| Arsenic (As)               | ≤ 3 ppm               |
| Cadmium (Cd)               | ≤ 1 ppm               |
| Mercury (Hg)               | ≤ 1 ppm               |
| Lead (Pb)                  | ≤ 10 ppm              |
| Expiration Date Period     | -----                 |
| 5 Years                    |                       |

Specification: PRD.0.ZQ5.10000048668

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at [Sigma-Aldrich.com](http://Sigma-Aldrich.com). For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.