


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com**Product Specification**Product Name:
Diethyl oxalate $\geq 99\%$

Product Number: 135364
CAS Number: 95-92-1
MDL: MFCD00009119
Formula: C₆H₁₀O₄
Formula Weight: 146.14 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Infrared spectrum	Conforms to Structure
Purity (GC)	$\geq 99.0\%$
Color Test	≤ 20 APHA

Remarks:

Specification Date : 06/21/2010

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.