

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.com

Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Octyl acetate - natural, ≥98%, FCC, FG

Product Number: W280615
CAS Number: 112-14-1
MDL: MFCD00009562
Formula: C10H20O2
Formula Weight: 172.26 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.418 - 1.421
Infrared spectrum	Conforms to Structure
Purity (GC)	≥ 98.0 %
Color test (APHA)	APHA < 100
Specific Gravity	0.865 - 0.868
Acid Value	≤ 1.0 ml
Solubility (Turbidity) 1ml/4ml, 70% Ethanol	Clear
Solubility (Color)	Colorless
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period 5 Years	-----

Specification: PRD.4.ZQ5.10000012941

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.