


3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
Ginkgolide B from Ginkgo biloba leaves - ≥90% (HPLC)

Product Number: G6910
CAS Number: 15291-77-7
MDL: MFCD05662347
Formula: C₂₀H₂₄O₁₀
Formula Weight: 424.40 g/mol
Storage Temperature: -20 °C



TEST	Specification
Appearance (Color)	White to Off-White
Appearance (Form)	Powder
Solubility (Color)	Colorless
Solubility (Turbidity)	Clear
50 mg/ml, DMSO	
Proton NMR spectra	Conforms to Structure
Purity (HPLC)	≥ 90 %
Recommended Retest Period	-----
3 years	

Specification: PRD.0.ZQ5.10000033585

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.