

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.com


Email USA: techserv@sial.com

Outside USA: eurtechserv@sial.com

Product Specification

Product Name:
Isovaleric acid - ≥99%, FCC, FG

Product Number: W310204
CAS Number: 503-74-2
MDL: MFCD00002726
Formula: C₅H₁₀O₂
Formula Weight: 102.13 g/mol



TEST	Specification
Appearance (Color)	Colorless
Appearance (Form)	Liquid
Refractive index at 20 ° C	1.401 - 1.405
Infrared spectrum	Conforms to Structure
Purity (Titration by NaOH)	99.0 - 101.0 %
Specific Gravity	0.922 - 0.927
at 25 Degrees Celsius	
Arsenic (As)	≤ 3 ppm
Cadmium (Cd)	≤ 1 ppm
Mercury (Hg)	≤ 1 ppm
Lead (Pb)	≤ 10 ppm
Expiration Date Period	-----
5 Years	

Specification: PRD.3.ZQ5.1000009021

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.