

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

5-Hydroxyindole-3-acetic acid (dicyclohexylammonium) salt - crystalline, ≥98% (TLC)

Product Number:

H2255

CAS Number:

66866-39-5

MDL:

MFCD00069704

Formula:


C₁₀H₉NO₃·C₁₂H₂₃N

Formula Weight:

372.50 g/mol

Storage Temperature:

-20 °C



TEST

Specification

Appearance (Color)

White to Off-White

Appearance (Form)

Powder

Solubility (Color)

Colorless

Solubility (Turbidity)

Clear

5 mg/mL, H₂O

Carbon

69.1 - 72.7 %

Nitrogen

7.2 - 8.7 %

Purity (TLC)

≥ 98 %

Specification: PRD.0.ZQ5.10000035411

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.